#### **Datasheet** HSA-Y-2-20 1 GHz High-Speed Amplifier MONITO HIGH-SPEED AMPLIFIER Features Bandwidth 10 kHz - 2 GHz • Exceptional low 10 kHz lower cut-off frequency for optimal pulse processing without shape distortion Rise time 175 ps . Gain 20 dB . Input return loss 23.1 dB . Integrated bias circuit . Monitor output Two identical signal outputs Applications Preamplifier for ultra-fast detectors (microchannel-plates, photomultipliers, • avalanche-photodiodes, PIN-photodiodes etc.) Oscilloscope and transient-recorder preamplifier Time-resolved pulse and transient measurements Block Diagram monitor amplifier DC - 100 kHz MONITOR 26 dB OUTPUT buffe OUTPUT INPUT 20 dF low noise buffe OUTPUT wideband bias amplifier DC-path 50 Ω BS-HSA-Y 23 R01 Intended Use The HSA-Y-2-20 amplifier is a fixed gain wideband GHz amplifier. It is designed for ultra fast amplification of small voltage and current signals in the frequency range from 10 kHz to 2 GHz. Operation is mostly self-explanatory. If in doubt, consult this document or contact support@femto.de. For safe operation, please refer to the damage thresholds specified in the "Absolute Maximum Ratings", "Temperature Range" and "Power Supply" sections of this document. **Application Notes** CAUTION! Do not exceed the maximum allowable input power of +13 dBm (20 mW). If in doubt, use attenuators on the amplifier input. The HSA-Y-2-20 offers two identical RF outputs. For operation it is mandatory that both RF outputs are terminated with 50 $\Omega$ loads. If only one output is used, the unused SMA output socket must be terminated with a 50 $\Omega$ terminator which is included in delivery. SOPHISTICATED TOOLS FOR SIGNAL RECOVERY Ц 0

### Datasheet

### HSA-Y-2-20

## **1 GHz High-Speed Amplifier**

Available Accessories	PS-15-25-L	Power supply Input: AC 100 – 240 V Output: DC ±15 V
Related Models	HSA-Y-1-40 HSA-Y-1-60 HSA-Y-2-40	Gain 40 dB, 10 kHz – 1 GHz, noise figure 1.9 dB Gain 60 dB, 10 kHz – 1.1 GHz, noise figure 1.9 dB Gain 40 dB, 10 kHz – 1.9 GHz, noise figure 4.9 dB
Specifications	Test conditions	$V_{\text{S}}=\pm15$ V, $T_{\text{A}}=25$ °C, system impedance 50 $\Omega,$ warm-up 20 minutes (min. 10 minutes recommended)
Gain	Gain Transimpedance gain Gain accuracy Gain drift vs. temperature	20 dB (× 10) 500 V/A (50 $\Omega$ input impedance × 10 gain) $\pm 1$ dB 0.015 dB/°C typ.
Frequency Response	Lower cut-off frequency (–3 dB) Upper cut-off frequency (–3 dB)	10 kHz 2 GHz
Time Response	Rise/fall time (10% - 90%) Group delay	175 ps 0.8 ns typ.
Input	DC input impedance RF input impedance 50 $\Omega$ noise figure Equ. input noise voltage Equ. input noise current Input reflection S11	50 Ω 50 Ω 5.2 dB (@ f <1 GHz) 680 pV/ $\sqrt{Hz}$ (@ f <1 GHz) 13.6 pA/ $\sqrt{Hz}$ (calculated: 680 pV/ $\sqrt{Hz}$ divided by 50 Ω) -23.1 dB (@ f <1.5 GHz) -16.5 dB (@ f <3 GHz)
Output	Two identical RF outputs: Output peak-peak voltage range Output power P <sub>1dB</sub> Output impedance Output reflection S22 Isolation between outputs	2 V ( $\pm$ 1 V) (@ <500 MHz, for linear amplification) +12.5 dBm (@ f <1 GHz) 50 $\Omega$ (terminate with 50 $\Omega$ load) -7.4 dB (@ f <3 GHz) 15 dB (@ f <3 GHz)
Monitor Output	Gain Monitor output impedance Lower cut-off frequency Upper cut-off frequency Output voltage	26 dB (1 kV/A) 50 $\Omega$ (terminate with ≥10 k $\Omega$ load, for best performance) DC 100 kHz ±10 V (@ 10 k $\Omega$ load)
Power Supply	Supply voltage Supply current	$\pm 15$ V ( $\pm 14.75$ V $\pm 16.5$ V) +160 / -10 mA typ. (depends on operating conditions, recommended power supply capability min. $\pm 250$ mA)
Case	Weight Material	190 g (0.42 lbs) including 50 $\Omega$ SMA terminator AIMg4.5Mn, nickel-plated
Temperature Range	Storage temperature Operating temperature	-40 °C +85 °C 0 °C +60 °C
Absolute Maximum Ratings	DC input voltage RF input power Power supply voltage	±4 V +13 dBm ±20 V
OPHISTICATED 1	L TOOLS FOR SIGNAL	RECOVERY FEDTO

## Datasheet

# **1 GHz High-Speed Amplifier**

	<u> </u>	
Connectors	Input RF Output Monitor output Power supply	SMA jack (female) $2 \times SMA jack (female)$ BNC jack (female) LEMO <sup>®</sup> series 1S, 3-pin fixed socket (mating plug type: FFA.1S.303.CLAC52) PIN2 $V_{s}$ $V_{s}$ $V_{s}$ $V_{s}$ PIN 1: +15 V Pin 2: -15 V Pin 3: GND
Scope of Delivery	HSA-Y-2-20, 50 Ω SMA te	erminator, LEMO® 3-pin connector, datasheet, transport package
Ordering Information	HSA-Y-2-20	High-speed GHz amplifier
0 P H I S T I C A T E D	TOOLS FOR SIGN	IAL RECOVERY FENTO

